

NETYS PL

User-friendly multi-socket protection

600 and 800 VA



Strong points

- > An innovative solution and superior design
- > Adapted protection to meet all your needs
- > Easy to use

Conformity to standards

- > EC/EN 62040-1, IEC/EN 62040-2
- > AS 62040.1.1, AS 62040.1.2, AS 62040.2
- > CE
- > RCM (E2376)

Technology

- > VFD "offline"

Certifications and attestations



Function

Compact and practical pluggable power protection integrating a larger number of sockets adapted to computer and IT peripherals in small office and home office environments, facilitating connection and tidier cabling.

Advantages

An innovative solution and superior design

- Modern design suitable for positioning over/under the desk or floor installations.
- Complementary USB port on the top for recharging mobile devices (e.g. phones, MP3, etc.).

Easy to use


- Operating mode indicated by means of the smart LED indicator lights.
- Easy battery maintenance and replacement.
- Integrated mains input cable on the side, allowing all six sockets to be used.

Adapted protection to meet all your needs


6 output sockets (French or German standards) for easy distribution directly to your applications:

- 4 sockets protected against power cuts and overvoltages, aimed at your most sensitive applications (professional desk top systems, workstation and monitors). The back-up time (up to 30 minutes) enables standard PC tasks and configuration to be saved.
- 2 sockets protected against overvoltage alone for use with less critical applications and high absorption consumers (e.g. laser printers).

Connections



Socket types



General characteristics

- USB port to charge mobile devices.



- Compact and practical pluggable power protection.
- Modern design suitable for positioning over/under the desk or floor installations.
- 6 output sockets (French or German standards) for easy distribution directly to your applications.
- LOCAL VIEW software for local UPS monitoring.
- USB port to charge mobile devices.

Standard communication features

- USB port for UPS management based on HID protocol.
- LOCAL VIEW software for local UPS monitoring and shutdown for Windows, Linux and MAC Osx.

Technical data

NETYS PL				
Model	NPL-0600-D	NPL-0600-F	NPL-0800-D	NPL-0800-F
Sn	600 VA		800 VA	
Pn	360 W		480 W	
Power (surge)	1200 VA			
Input/output	1/1			
INPUT				
Rated voltage	230 V			
Voltage tolerance	180 ÷ 270 V			
Rated frequency	50/60 Hz with automatic selection			
Mains connection	Cable with plug			
OUTPUT				
Rated voltage	230 V ±10%			
Rated frequency	50/60 Hz ±1%			
Wave form	Step wave			
Protection	Overload, significant discharge and short circuit			
Sockets	4 sockets for UPS and surge protection, 2 sockets for surge protection			
Socket standard	German	French	German	French
BATTERIES				
Type	Sealed lead-acid maintenance free - expected life 3/5 years			
Back-up time ⁽¹⁾	15 min		20 min	
COMMUNICATION				
Interfaces	USB			
Local communication software	Local View			
UPS CABINET				
Dimensions WxDxH	220x220x123 mm			
Weight	3.6 kg		4.1 kg	
Colour	Black		White	
STANDARDS				
Safety	IEC/EN 62040-1, AS 62040.1.1, AS 62040.1.2			
EMC	IEC/EN 62040-2, AS 62040.2			
Product declaration	CE, RoHS (E2376), UKCA			

(1) PC+17" LCD monitor.